

Features

- \square 360° molded, low resistance, high output diffuser head design
- ☐ Connecting tower design
- ☐ Large, quad wing nut connector
- ☐ Audible pop-off alarm 3PSI or 6PSI
- ☐ Jar permanently etched, large print minimum/maximum water level markings
- ☐ Easy seal, translucent, double helix thread jar


Benefits

- ☐ Quiet, efficient hydration with less rain out. Resists clogging due to mineral build up from water.
- ☐ Greater resistance to damage from incidental impact
- ☐ Easy to grip, reduces chance of cross-threading
- ☐ Reduces the likelihood of concentrator damage. Audible warning of downstream occlusion.
- ☐ Easy to read, durable will not rub, wear or wash off
- ☐ Simple, sure, half turn on/off with positive seal. No gasket is required




Salter Humidifiers P/N 7100 3psi pop off P/N 7600 6psi pop off

Disposable Humidifiers from Salter Labs are single patient use products designed and engineered for long term durability and complete patient satisfaction.





Start-up Kit Available with P/N 7100 or P/N 7600 Humidifier



Unique 360° rectangular diffusion ports operate quietly with improved hydration and less system back pressure.

Ordering Information

	Units (per case)		Part No.	
Humidifier			3 _{PSI}	6PSI
350 cc bubble humidifiers 350 cc bubble humidifiers		50 50	7100	7600

For high flows (6-15 lpm) refer to our model #7900 Bubble Humidifier.

Start-up Kits

2 #1606 nasal cannulas, 1 #7100 or #7600 humidifier and 1 #2002 supply tube:

Kit with a 7' tube	20	7107	7607
Kit with a 25' supply tube	20	7125	7625
Kit with a 50' supply tube	20	7150	7650

Start-up Kits with smooth bore tubing available on request



100 W. Sycamore Road - Arvin, CA 93203 Phone: 661-854-3166 1-800-421-0024 1-800-235-4203 Fax: 661-854-3850 Toll Free Fax: 1-800-628-4690 Fax: 661-854-3850 E-mail: salterlabs@us.salterlabs.com www.salterlabs.com

0482